

Adapter cable set

111.7028

For current clamps and sensors with 4mm plugs (connection to the AUX-Port of PQ-Box 200)



1. Use

This device is used for the connection of current clamps and sensors to the AUX-Port of PQ-Box 200 with 4mm banana plugs.

The free adapter cable set enables to use additional current clamps or sensors for the PQ-Box. The input current range lies at 1000 mV AC resp. 1400 mV DC.

Caution:

For usage of current clamps/sensors with voltage output only. Current clamps with current output may cause destruction of the PQ-Box.

2. Structure

The flexible and shielded measurement cable consists of a cable with 7-pole Amphenol plug on one end and 2 x 4 mm banana plugs on the other end.

3. Dimensions and weight

| Length in mm | 2000 | |
|--------------|------|--|
| Weight in g | 100 | |

4. Technical Data

| Voltage: | Max. 30V |
|----------------|-------------|
| Cross-section: | 2x0,5mm² |
| Plug: | Amphenol |
| Voltage class: | Low-voltage |

5. Ordering Information

| FEATURE | ORDER CODE |
|----------------------------------|------------|
| Adapter cable set | 111.7028 |
| Adapter cable, 2-pole, Length 2m | |

A. Eberle GmbH & Co. KG

Frankenstraße 160 D-90461 Nürnberg

Tel.: +49 (0) 911 / 62 81 08-0 Fax: +49 (0) 911 / 62 81 08 96 E-Mail: info@a-eberle.de http://www.a-eberle.de

Version: 11/6/2017 9:18 AM

Copyright 2013 by A. Eberle GmbH & Co. KG

Subject to change without notice.